

Mount Type
Column
1

Mag. Factor
Column
2

Scope Brand
Column
3

Scope Model
Column
4

DC
"C" MOUNT

38
(0.38X)
1/3" Chip,
6mm diag

50
(0.50X)
1/2" Chip,
8mm diag

67
(0.67X)
2/3" Chip,
11mm diag

10
(1.0X)

DS
SONY
1/2" Bayonet

10
(1.0X)

for Olympus "U" and
Zeiss "Z" models only

DH
1/2" Bayonet

10
(1.0X)

for Olympus "U" and
Zeiss "Z" models only

DB
2/3" Bayonet
(ENG)

10
(1.0X)

for Olympus "U" and
Zeiss "Z" models only

DE
EOS Bayonet

10
(1.0X)

for Olympus "U" and
Zeiss "Z" models only

DF
F-Mount

10
(1.0X)

for Olympus "U" and
Zeiss "Z" models only

DZ
C-Mount

ZOOM
31
(3:1)
Zoom Ratio
(0.33X - 1.0X)

Recommended for
1/3" Cameras.
Refer to Page 23

L
LEICA
(Leitz, Wild,
Bausch & Lomb)

N	LEICA INVERTED	• DMIL (inserts into 38mm ISO photoport)
	LEICA STEREO	• MS5 • MZ6 • MZ8 • MZ12 • MZAP0 (ALL insert into 38mm ISO photoport) • GZ6 (w/Phototube #13410302)
	LEITZ UPRIGHT	• Aristomet • Aristoplan • Dialux • Diaplan • Ergolux • Laborlux • Metallux • Ortholux • Orthoplan (ALL insert into 38mm ISO photoport)
	LEITZ INVERTED	• Diavert • Fluovert • Labovert • Metallovert (ALL insert into 38mm ISO photoport)
P	WILD STEREO	• M3 • M5 • M7 • M8 • M10 (ALL insert into 38mm ISO photoport)
	WILD MACROSCOPE	• M420 (inserts into 38mm ISO photoport)
	LEICA COMPOUND	• DM L Series • DM R Series • DM RD (does NOT fit Photo TV Module) • FSA Tube Adapter • TV Tube Adapter • Variotube (ALL insert into 37mm photoport, ALL Delta Optics Series with 37mm photoport)
R	LEICA STEREO	• MS5 • MZ6 • MZ8 • MZ12 • MZAP0 (ALL w/ 37mm photoport) • GZ6 (w/ Phototube #13410309)
	LEICA/B&L UPRIGHT	• Balplan • Microzoom
S	LEICA/B&L STEREO	• SZ-6 • StereoZoom 6
	LEICA/B&L STEREO	• SZ-7 • StereoZoom 7 (w/ Slip-in port)
Y	LEICA COMPOUND	• DM L Series • DM R Series • DM IR Series • DM IL Series (ALL HC Optics Series)

M
MITUTOYO

T	UPRIGHT	• Finescope 60
----------	---------	----------------

N
NIKON

N	UPRIGHT	• Alphaphot-2 • Eclipse Series (requires YT-Tube 92306) • Labophot-2 • Optiphot-2 • Optiphot 100S, 150, 200, 300 (ALL insert into 38mm ISO photoport)
	INVERTED	• Diaphot 300/200 • TS100-F • TE2000 (ALL insert into 38mm ISO photoport and are incompatible with 0.38X and 0.5X mag. couplers)
	METALLURGICAL	• Epiphot 300/200 (inserts into 38mm ISO photoport)
	STEREO	• SMZ-10A (0.67X and 1.0X only) • SMZ-U • SMZ-800 • SMZ-1000 • SMZ-1500 (ALL insert into 38mm ISO photoport)
	MEASURING	• MM-40 • MM-60 (both insert into 38mm ISO photoport)

O
OLYMPUS

U	UPRIGHT	• AX Provis Series • BX Series • BX2 Series • CX Series • CX2 Series • MX Series (ALL w/ U-SPT phototube removed) • BX U-DPT Double Port (back port only, front port uses "H" Bottom Clamp from Standard Series, See Page 10)
	STEREO	• SZX Series (ALL w/ U-SPT phototube removed)
W	INVERTED	• IX Series (sideport or trinocular head [U-TR30H])

Z
ZEISS

M	UPRIGHT	• Axiophot • Axioplan • Axioskop • Axiotron
	INVERTED	• Axiovert 10 • Axiovert 35 • Axiovert 35M • Axiovert 405M
Z*	UPRIGHT	• Axiolab • Axiophot-2 • Axioplan-2 • Axioskop-2 • Axiostar • Axiotech • STD 25 ICS • KF2 ICS • New Standard Trinocular Tube (Zeiss # 452902)
	INVERTED	• Axiovert 100 • Axiovert 135 • Axiovert 135M • Axiovert 200 (ALL non-compatible w/ 0.38X mag.) • IM Series (w/ new Standard Trinoc Tube [Zeiss # 452902])
	STEREO	• Stemi DRC (w/ 455005 phototube) • Stemi 2000-C • Stemi 2000-CS • SV6 • SV11
O	UPRIGHT	• Axiomat • Photomicroscope II & III • UEM • Ultraphot IIIB • Universal (replaces phototube in ALL models)

* 0.38X Coupler requires 22.0mm clearance depth in Trinoc Tube

Mount Type Mag. Factor

Scope Brand Scope Model

How To Use The Model Makers

- 1 Indicate your desired 2-letter Camera Mount Type from column #1.
- 2 Indicate the desired 2-digit Magnification Factor from column #2.
- 3 Indicate your 1-letter Microscope Brand from column #3.
- 4 Indicate your 1-letter Microscope Model from column #4.